Lo-Boy Whirlpools

Use



L Series 75 Gallon Stationary Whirlpool L-75-S



Product photo/image above may show some available options

L-75-S Stationary Whirlpool is recommended for treatment of extremities, hip and back area. It is ideal for pediatric and geriatric applications imparting a greater degree of patient comfort and safety.

Tank Capacity is 75 gallons.

Whirlpool Tank is 52"L x 24"W x 18"D and is seamless welded construction, fabricated from heavy gauge, type 304 stainless steel, polished to a satin finish. Tank rim is reinforced with a concealed stainless steel rod. Tank bottom is seamless, rounded coved design to minimize bacteria buildup. Tank is also provided with an extended stainless steel skirt flush to the floor line to conceal internal drain piping.

A 2" Combination Drain and Overflow, and a Filler Spout are provided. (See roughing-in dimensions on the reverse side).

Turbine Raising and Lowering Device permits adjustment of desired height and direction of water agitation towards the area of the body to be treated. It is spring balanced and provided with a locking device.

Turbine Assembly functions both as agitator and emptying device. It is equipped with Underwriters Laboratory listed 1/2 HP jet pump motor protected with an ABS plastic shell, and automatic thermal overload protector, and lifetime-sealed bearings.

All parts contacting the water are stainless steel, chrome plated brass or bronze.

Thermometer is provided with a dual scale, adjustable calibration, and a stem inserts into a retainer to prevent rattle during whirlpool agitation.

GUIDE SPECIFICATIONS

Provide Stationary Whirlpool (specify model number and options) with a 75-gallon capacity, 52"L x 24"W x 18"D. Whirlpool shall be fabricated from heavy gauge, type 304 stainless steel. Construction shall be seamless welded and exposed surfaces shall be polished to satin finish. Tank shall have a reinforced rim and shall be fitted with a stainless steel skirt flush to the floor line. Bottom of tank shall be a seamless, rounded coved design to minimize bacteria build up. Provide a 2" combination drain and overflow, and a filler spout. Provide a turbine assembly with raising and lowering device which functions both as agitator and emptying device, permits adjustment of desired height, direction of water agitation, and can be locked into place. Turbine assembly shall be UL listed 1/2 HP jet pump motor with automatic thermal overload protector, and lifetime-sealed bearings. Provide a 3" dial thermometer with a stem retainer to prevent rattle when whirlpool is in operation.





Lo-Boy Whirlpools

Series

O -L Lo-Boy Series

O -75 Gallons

O -S Stationary Whirlpool

Suffix Options (See Whirlpool Option Section for Details)

- O -ALC Adjustable Low Chair
- O -ALS Adjustable Low Stool
- O -ARS Arm Rest Support
- O -AS3 Adjustable Suspension Seat
- O -CTS3 Combination Table with Side Seats
- O -EG Enviro Glaze Color Powder Coating -Specify Color:

(Special Finish Consult Factory)

MODEL NUMBER AND OPTION SELECTIONS

- O -GFI Ground Fault Interrupter
- O -HR Head Rest, Adjustable
- O -MXT1 Thermostatic Mixing Valve (15 G.P.M.)
- O -MXT2 Thermostatic Mixing Valve (25 G.P.M.)
- O -MXWH Washout Hose Attachment for MXT Valves
- O -PCS Pump Cover Strainer
- O -PHS2 Patient Handling System (Chair Type)
- O -RHG Rubber Hand Grips
- O -RS Reclining Seat
- O -SDO Separate Drain and Overflow Assembly
- O -TTS2 Tank Top Seat

Turbine Assembly

Electrical on standard turbine supplied is 115 V 60 Hz if 220 V is required please specify:


O 50 Hz O 60 Hz


All dimension figures in parentheses are in millimeters.

ELECTRIC REQUIREMENTS: Amps: 8 Volts: 115 Hertz: 60 GFI Receptacle



	VALVE	INLETS	OUTLET	DIM A	DIM B	DIM C
1	MXT1 (15 GPM)	1/2" NPT	1/2" NPT	8-1/2" (215)	13-3/4" (350)	18" (455)
	MXT2 (25 GPM)	3/4" NPT	3/4" NPT	9-1/2" (240)	13-1/2" (345)	17" (430)





STATIONARY L-75-S SERIES WHIRLPOOL

NOTES:

- 1. 1/2 hp Jet Pump Motor.
- 2. Variable Pressure Control.
- Thermometer.
- Turbine Raising & Lowering Device.
- 5. Combination Drain & Overflow Assembly.
- 6. "L" Brackets —Four Each.
- 7. Stainless Steel Tank. 8. 2" O.D. x 5" Tail Piece.
- 9. 3 Pole GFI Receptacle by Others.
- 10. Floor Drain by Others.
- 11. Optional Thermostatic Mixing Valve with Vacuum Breaker.
- 12. H & C Water Inlets by Others.
- 13. Filler Spout.

SELECTION SUMMARY & APPROVAL FOR MANUFACTURING
--

Model Number & Options_ Company_ Date Title Contact Approval for Manufacturing/Signature