

## VACUUM ACCESSORIES





# The Roll Stand and other accessories make life easier using our vacuum devices.

#### It's Convenient.....

The suction roll stand provides suction where and when you need it, either from a wall suction source or portable aspirator. It is easily used in hospitals, surgical suites, sub-acute, homecare and long term care facilities.

#### It's Versatile.....

The shelf on the PM60-2 roll stand is large enough to securely accommodate any of the Precision Medical, Inc. portable aspirators. The aspirators are easily attached to the shelf by means of the durable Velcro™ strap making it interchangeable if needed. Or, the units can be

permanently mounted to the shelf. The attached universal canister bracket allows the use of four suction canisters.

#### It's Easy to Maintain...

The compressor shelf is powder coated and durable. The pole, base arms and casters are smooth, easy-to-clean and infection control friendly.

#### It's Unique...

The SCS-2000 Model has a ball-pivot holder for attachment of the suction regulator. This allows movement of the regulator in any direction making visual observation of the suction rate easier. The four-port, on-off valve allows quick change from canister-to-canister during the suctioning process.

#### It's Sturdy...

The five-arm base of the stand along with the high quality casters provides a sturdy stand that is virtually impossible to tip over during normal use.

#### PM60-2 Roll Stand \*



The Roll Stand allows you to easily move a suction unit from room to room allowing easy placement anywhere. The stand shelf is large enough to accommodate any of Precision Medical's air compressors, aspirators or nebulizer compressors. The universal canister holder can accommodate numerous canister configurations.

#### SCS2000 Suction Roll Stand \*



pivot holder for attachment of the suction regulator. This allows movement of the regulator in any direction making visual observation of the suction rate easier. The four-port, on-off valve allows quick change from canister-to-canister during the suctioning process. The universal canister holder can accommodate numerous canister configurations.

#### **Canisters**



Canisters come in 3 sizes: 800cc, 1200cc and 2000cc. A self sealing lid provides a leak-free seal when vacuum is applied. An automatic float shut-off provides protection against canister overflow.

#### **Ordering Information:**

1906-12 1200cc (Case of 12) 502519-10 800cc (Case of 10) 502687-12 2000cc (Case of 12)

#### Suction Tubing, Filter Assemblies & **Hydrophobic Filter**



Suction Tubing comes in a 6' length.



Hydrophobic Filters provides final filtration and overflow protection.

#### **Ordering Information:**

1690 Hydrophobic Filter 1955

Suction Tubing
Inline Filter & Tubing Assembly (PM60-2) 502690

503477 Filter Assembly, SCS2000

#### PM9000 Vac Trap



The Vac Trap protects suction regulators and central vacuum systems from accidental contamination by liquid overflow from suction collection canisters. This unique design assures positive shut-off at low as well as line vacuum conditions. Various configurations are available for attachment to vacuum regulator or central vacuum system.

\*All Roll Stands are sold without Aspirators, Canisters or Vacuum Regulators.

### ADDITIONAL ORDERING INFORMATION

Description	Part#
PowerVac Aspirator	PM61
PowerVac+ Aspirator	PM63
Vacuum Regulator (2 Mode Continuous)	PM3000 Series
Vacuum Regulator (3 Mode Continuous)	PM3100 Series
Vacuum Regulator (Continuous/Intermittent)	PM3300 Series
Vacuum Regulator (Pediatric Continuous/Intermittent)	PM3400 Series



