

PO: _____	Date: _____	Customer #: _____
Customer Name: _____	Ship To Name: _____	
Address: _____	Address: _____	
Phone: _____	Phone: _____	
Contact: _____	Contact: _____	
Email: _____	Tag: _____	



Standard Features
<ul style="list-style-type: none"> · Tubular Steel, Powder Coated Frame · 45 Degrees, Infinitely Adjustable Seat Tilt · Fixed Height Arm Supports · Adjustable Seat Depth 16" - 20" · Adjustable Seat Surface Height 14" - 19" · Choice of Wheel, Caster and Fork Sizes · Push Lock Parking Brakes
<ul style="list-style-type: none"> · Drop In, Swing Away Lower Leg Supports · Composite Foot Support Plates · Cushioned Side Panels · Adjustable Backrest Angle · 250 lbs. Maximum Occupant Weight · Seat, back and head support cushions not included

Comfort Rehab Wheelchair (587) - (E1161)

HCPCS codes supplied are for reference only and do not ensure coverage or payment. The HCPCS provided are based on our interpretation of the code definitions. HCPCS codes are not intended to be, nor should be considered billing or legal advice. Providers are responsible for determine the appropriate billing codes when submitting claims to the Medicare Program and should consult an attorney or other advisor to discuss specific situations in further detail.


Frame Color Options

Black
 Blue
 Bronze
 Nickel
 Red
 Orange
 Sand
 Yellow
 Pink
 Purple

Seat and Back Options

Seat Width:	Seat Depth:	
<input type="radio"/> 16" <input type="radio"/> 18" <input type="radio"/> 20" (E2201) <input type="radio"/> 22" (E2201) <input type="radio"/> Solid Seat Pan (E2231) Factory Installed <input type="radio"/> Omit Seat Pan	<input type="radio"/> 16" <input type="radio"/> 17" <input type="radio"/> 18" <input type="radio"/> 19" <input type="radio"/> 20" (E2203)	N/C N/C N/C N/C N/C

Seat Surface Height:	Back Cane Height:
<input type="radio"/> 14" <input type="radio"/> 14.5" <input type="radio"/> 15" <input type="radio"/> 15.5" <input type="radio"/> 16" <input type="radio"/> 16.5" <input type="radio"/> 17" <input type="radio"/> 17.5" <input type="radio"/> 18" <input type="radio"/> 19"	<input type="radio"/> Ultra-Low Double Bend (16") Fixed <input type="radio"/> Ultra Low (16") Fold Down <input type="radio"/> Low (18") Fold Down <input type="radio"/> Medium (21") Fold Down <input type="radio"/> Tall (24") Fold Down
N/C N/C N/C N/C N/C N/C N/C N/C N/C N/C	<input type="radio"/> 5° <input type="radio"/> 10° <input type="radio"/> 15° <input type="radio"/> 20°



Refer to Seat Surface Height and Wheel Combinations Matrix for assistance.

Front Mount Options Wheel Options Rear Mount Options

<input type="radio"/> 5" Fixed Caster Wheels - Pair Standard <input type="radio"/> 6" Fixed Caster Wheels - Pair N/C <input type="radio"/> 8" Fixed Caster Wheels - Pair N/C	<input type="radio"/> 20" Mag Wheels - Pair Standard <input type="radio"/> 22" Mag Wheels - Pair N/C <input type="radio"/> 24" Mag Wheels - Pair N/C	
---	---	--

Caster Wheel Forks: Required	Mag Wheel Position: Factory Set (Adjustable in the future)
<input type="radio"/> Small - Recommended for Small Mag Wheel (20" or 22") and Lower Seat Surface Heights N/C <input type="radio"/> Medium - Recommended for Large Mag Wheel (24") Higher Seat Surface Heights N/C	<input type="radio"/> A (Most Forward) - Smaller Turning Radius N/C <input type="radio"/> B N/C <input type="radio"/> C N/C

Refer to Seat Surface Height and Wheel Combinations Matrix for assistance.

Parking Brake Extension Handles (pair) (E0961)
 Anti-Tip Devices (E0971) - Required Safety Features - Factory Installed

Arm Support Options

Fixed Height Arm Supports Standard
 Height Adjustable, Removable Arm Supports (E0973)

Lower Leg Support Assembly and Lower Leg Support Options

Lower Leg Support Assembly Style: <i>must choose one</i>	Lower Leg Support Accessories:
<input type="radio"/> Drop In Straight - Pair N/C <input type="radio"/> Drop In Flared - Pair N/C <input type="radio"/> Pin and Saddle Straight - Pair N/C <input type="radio"/> Pin and Saddle Flared - Pair N/C <input type="radio"/> Drop In IKON Style - Pair N/C <input type="radio"/> F-SW75ADJ-587V3 Swing Away 75° Lower Leg Supports - Pair NC <input type="radio"/> F-SW60ADJ-587V3 Swing Away 60° Lower Leg Supports - Pair NC <input type="radio"/> F-SW-1KN Swing Away Lower Leg Supports Silver - Pair NC <input type="radio"/> F-SW-1KN-ADJ Swing Away Lower Leg Supports Black NC <input type="radio"/> Steel w/ Angle Adjustable Flip-up Foot Supports - Pair (K00- <input type="radio"/> 2" Extended Footrest Tubes - <i>Only compatible on the F-SW-1KN and F-SW-1KN-ADJ</i>	<input type="radio"/> Posterior Foot Supports - Pair E0951 <input type="radio"/> Lower Leg Support Panel (for calf support) E0995 <input type="radio"/> Lower Leg Support Foot Board <input type="radio"/> F-SW-ELV Swing Away, Elevating Lower Leg Supports Black - Pair (E0990) <input type="radio"/> F-SW-LL-1KN Swing Away, Elevating Lower Leg Supports Silver - Pair (E0990) <input type="radio"/> F-SW-ANGLE Aluminum w/ Angle Adjustable Flip-up Foot Supports - Pair (K00- Swing Away, 70 Degree Lower Leg Support W/ Angle Adjustable Footplates, Black - Pair (K0040)

Common Accessories

Pelvic Belt	<input type="radio"/> Ctr Buckle <input type="radio"/> Side Buckle
<input type="radio"/> Pelvic Positioning Strap Grommet Mount (E0978)	
Trays:	<input type="radio"/> Sewn Strap <input type="radio"/> Grey <input type="radio"/> Black <input type="radio"/> Tray ABS with Strap (E0950) (16", 18" 20" 22" - Matches Corresponding Seat Width) <input type="radio"/> Tray ABS Cushioned Cover <input type="radio"/> Clear Tray with Strap (E0950) (16", 18", 20" - Matches Corresponding Seat Width) <input type="radio"/> Sewn Strap
Other:	<input type="radio"/> Front Mounted OR <input type="radio"/> Rear Mounted <input type="radio"/> IV Pole and Assembly - (K0105) <input type="radio"/> Oxygen Holder and Assembly (E2208) <input type="radio"/> Accessory Bag (Black) Each <input type="radio"/> Accessory Bag Personalizing 2 Initials <input type="radio"/> Brush Font OR <input type="radio"/> Block Font <input type="radio"/> O2-HOLDER-BAG Oxygen Holder, Soft Carry Bag <input type="radio"/> Cup Holder

Matrix® Seating Series

Matrix® Seat Cushions

For Correct Fit: Cushion Size Should Match Selected Chair Seat Dimensions

Seat Cushion Depth: 16" 18" 20" 22" (Only available w/Multi & PS Cushions)

Seat Cushion Width: 16" 18" 20"

- Libra (E2624)** - Recommended for highest risk of or existing skin breakdown
- Multi (E2607)** - Recommended for moderate to high risk of skin breakdown
- Vi (E2607)** - Recommended for moderate to high risk of skin breakdown
- PSP (E2607)** - Recommended for moderate to high risk of skin breakdown
- PS (E2605)** - Recommended for low to moderate risk of skin breakdown

- Libra Cushion Accessories:**
- Libra Fluid Supplement**
 - Libra 1" Hemi Wedge**
 - Libra 1" Anterior Seat Wedge**
 - Libra Tapered Wedge Left**
 - Libra Tapered Wedge Right**
 - Libra Abductor**

Seat Cushion Width: 22"

- Libra (E2625)** - Recommended for highest risk of or existing skin breakdown
- Multi (E2608)** - Recommended for moderate to high risk of skin breakdown
- Vi (E2608)** - Recommended for moderate to high risk of skin breakdown
- PS (E2606)** - Recommended for low to moderate risk of skin breakdown

Multi, Vi, PSP & PS Cushion Accessories: Pelvic Obliquity Kit \$50

Cushion Rigidizer:	E0992	16" Depth	18" Depth	20" / 22" Depth
All Cushions	16" Width			
	18" Width			
	20" Width			
	22" Width			

Matrix® Backs

For Correct Fit: Back Size Should Match Selected Chair Seat Dimensions

Back Height: 16" 18" (excludes PB & PB Deep) 20"

Back Width: 16" 18" 20"

- E2 (E2615)** - Recommended for users seeking optimal immersion and airflow
- E2 Deep (E2620)** - Recommended for users seeking optimal immersion w/ contoured support needs 5/75
- Elite TR (E2620)** - Recommended for tilt in space & recline applications
- Elite (E2620)** - Recommended for more active users
- Elite Deep (E2620)** - Recommended for active users with contoured support needs
- PB (E2615)** - Recommended for less active users seeking comfort
- PB Deep (E2615)** - Recommended for less active users seeking comfort & support

- E2 Back Accessories:**
- E2 Fixed Lateral Supports 6.5"Hx5"L (Pair) (E0956)**
 - E2 Chest Harness Interface**
 - E2 Contoured Backbone Lumbar/PSIS Support**
 - E2 PostureFlex Abdominal Support 7"Hx20"-32"L**
 - Quad Release Tab for PostureFlex**
- Back Slipcovers:**
- E2 Infection Control Slipcover**
 - E2 Deep Infection Control Slipcover**
 - Infection Control Slipcover for Matrix Cushions**

Back Width: 22"

- Elite TR (E2621)** - Recommended for tilt in space & recline applications
- Elite (E2621)** - Recommended for more active users
- Elite Deep (E2621)** - Recommended for active users with contoured support needs

- Matrix Back Military Service Decals:**
- Air Force
 - Army
 - Marine
 - Navy

- Privacy Flap Accessories:**
- 16" Width Small Privacy Flap
 - 18" Width Medium Privacy Flap
 - 20" Width Large Privacy Flap
 - 22" Width Extra Large Privacy Flap

- Lateral Support Accessories:**
- Elite Back Fixed Laterals 5"Hx7.5"L (E0956)**
 - Elite Back Swing Away Lateral Hardware (E1028)**
 - Swing Away Lateral Pad (Each) 4.25"Hx6.5"L (E0956)**

Matrix® Headrest

- Head Support Mounting:**
- Elan Head Support Hardware (E1028)** - Required with Selection of Head Support
 - Elan Flipp Head Support Hardware (E1028)** - Required with Selection of Head Support
 - Loxx Head Support Hardware (E1028)** - Required with Selection of Head Support
 - Loxx Flipp Head Support Hardware (E1028)** - Required with Selection of Head Support
- Choose One**

- Support Options:**
- Head Support Cushion (E0955)** 10" 14"
 - Hug Head Support Cushion (E0955)** 10" 14"
 - Head Support 4 Point Cushion (E0955)** 9" x 7" 11" x 10"
 - Headband with 4 Point Cushion (E0955)** Small Large

Additional Options:

Delivery Instructions or Special Requests:

Total: \$

Accessory Services: Each with an additional charge, are available to accommodate the delivery needs of Broda customers and/or the needs of a shipment's final delivery location. **To ensure a seamless delivery of each Broda order,**

- any accessory services needed to deliver are requested when an order is submitted to Broda.**
 - Lift Gate Service:** Delivery is made with a lift gate trailer that moves the shipment from trailer level to ground level
 - Residential Delivery Service:** Delivery to a residential location
 - Notification Before Delivery:** Contact is requested to the Consignee by the Carrier PRIOR to shipment delivery
 - Inside Delivery Service:** Movement of the shipment beyond the unloading position, i.e. move closer to a door, inside a building.
 - upstairs, down a hall, etc.** Price is specific per order, based on the customer's inside delivery needs.
 - Limited Access Service:** Delivery locations that are not open to the walk-in public, during normal business hours. Mon-Fri. 8a-5p
- Expedited delivery is available by customer request at the time of order, which is priced per order and is based on the delivery location and level of service.*

Knee-to-Heel Range (Comfort Rehab ONLY)			
Front Rigging Model	Description	Minimum	Maximum
Range Adjusts in 3/4" increments			
F-SW 75-587V3	75° Drop-in, black	14.25"	17.25"
F-SW 75ADJ-587V3	75° Drop-in w/ angle adjustable footplates, black	14.25"	17.25"
F-SW 60ADJ-587V3	60° Drop-in w/ angle adjustable footplates, black	15"	18"
F-SW-ELV-587V3	Drop-in, elevating, black	15"	18"
F-SW-ELV-ANGLE-587V3	Drop-in, elevating w/ angle adjustable footplates, black	15"	18"

587V3: SEAT HEIGHT & WHEEL COMBINATIONS									
SEAT HEIGHT	MAG WHEEL	CASTER WHEEL	CASTER FORK	MAG PLATE HOLE #	CASTER FORK HOLE #	ANTI-TIPPER MOUNT	ANTI-TIPPER HOLE #	SEAT TAB	
14"	20	5	SMALL	1	1	TOP	3	2	
	22	5	SMALL	2	2	TOP	2	1	
15.5"	20	6	MEDIUM	2	1	TOP	2	1	
	22	6	MEDIUM	1	1	TOP	2	1	
	24	6	SMALL	1	2	TOP	1	1	
	24	5	MEDIUM	1	2	TOP	1	1	
16"	24	6	MEDIUM	1	1	TOP	1	1	
	20	5	SMALL	3	3	TOP	1	1	
	20	5	MEDIUM	3	3	TOP	1	1	
	20	6	MEDIUM	3	2	TOP	1	1	
16.5"	22	5	SMALL	2	3	TOP	1	1	
	22	6	SMALL	2	2	TOP	1	1	
	22	5	MEDIUM	2	3	TOP	1	1	
	22	6	MEDIUM	2	2	TOP	1	1	
17"	24	5	SMALL	1	3	TOP	1	1	
	20	6	SMALL	3	3	TOP	1	1	
	24	6	SMALL	2	3	BOTTOM	3	1	
	24	5	MEDIUM	2	4	BOTTOM	3	1	
17.5"	24	6	MEDIUM	2	3	BOTTOM	3	1	
	20	5	MEDIUM	4	5	BOTTOM	3	1	
	20	6	MEDIUM	4	4	BOTTOM	3	1	
	22	5	MEDIUM	3	5	BOTTOM	3	1	
18"	22	6	MEDIUM	3	4	BOTTOM	3	1	
	20	8	SMALL	4	3	BOTTOM	3	1	
	22	8	SMALL	3	3	BOTTOM	3	1	
	24	6	MEDIUM	3	5	BOTTOM	2	1	
19"	24	8	MEDIUM	3	3	BOTTOM	2	1	
	20	8	MEDIUM	5	4	BOTTOM	2	1	
	22	8	MEDIUM	4	4	BOTTOM	2	1	

Hole numbering begins at the top of the plate, fork and anti-tipper. Hole number 1 is the uppermost hole.
Do not use the rear most vertical row/column of holes on the mag plate for 20" mag wheels

Form08CONFIG- 404 587V3 Rev. 1
